





program č. 6

2021 SYC KANSAS MEDIUM



| | | | |
|--------------------|--------------------------|-----------------|-----------------|
| DISTANCE: | 42 FEET | VOLUME: | 25.76 mL |
| RATIO: | 4.41:1 | FORWARD: | 18.41 mL |
| DROP BRUSH: | 40 FEET | REVERSE: | 7.35 mL |
| TANKS: | KEGEL & KEGEL | PUMP: | MULTI |




FORWARD LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L | 2R | 5 | 40 | 18 | 3 | A - Kegel | 0 → 10 | 7,400 |
| 2 | 6L | 6R | 2 | 45 | 18 | 3 | B - Kegel | 10 → 15 | 2,610 |
| 3 | 9L | 9R | 2 | 50 | 18 | 3 | A - Kegel | 15 → 20 | 2,300 |
| 4 | 10L | 10R | 4 | 50 | 18 | 3 | B - Kegel | 20 → 30 | 4,200 |
| 5 | 11L | 11R | 2 | 50 | 22 | 3 | A - Kegel | 30 → 36 | 1,900 |
| 6 | 2L | 2R | 0 | 50 | 26 | 3 | B - Kegel | 36 → 42 | 0 |

REVERSE LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L | 2R | 0 | 50 | 26 | 3 | A - Kegel | 40 → 28 | 0 |
| 2 | 12L | 12R | 2 | 50 | 22 | 3 | B - Kegel | 28 → 22 | 1,700 |
| 3 | 10L | 10R | 3 | 50 | 22 | 3 | A - Kegel | 22 → 13 | 3,150 |
| 4 | 8L | 8R | 2 | 50 | 18 | 3 | B - Kegel | 13 → 8 | 2,500 |
| 5 | 2L | 2R | 0 | 50 | 14 | 3 | A - Kegel | 8 → 0 | 0 |



THIS PATTERN IS DESIGNED FOR:
 VARIABLE MICROLITER STREAMS | DUAL CONDITIONING TANKS | REVERSE DROP BRUSH
 This pattern may require adjustments if using a lane machine that does not have these features

SCAN QR CODE TO
 SHARE AND
 DOWNLOAD
 THIS PATTERN



KEGEL PATTERN LIBRARY APP
 GET IT ON Google Play | Download on the App Store

PATTERNLIBRARY.KEGEL.NET